




磁性识别传感器




BS05C1HFAA
BS05C1HGCA




BS05M1HFAL





BS05N1HFAA
BS05N1HGAA
BS05N1NFAA




BS05M1KFBB



BS05M1KFCA
BS05M1KGCA



BS05W1KFAA
BS05W1KFAB



品名	电源电压 (V)	最小输出电压	最大输出电压	检测宽度 (mm)	动作温度范围 ()
BS05C1HFAA	5	400mV rms	-	3	-20 to 60
BS05C1HGCA	5	235mV rms	405mV rms	3	-20 to 60
BS05M1HFAL	5	150mV rms	-	3 x 8ch	0 to 50
BS05N1HFAA	5	400mV rms	-	3	-20 to 60
BS05N1HGAA	5	235mV rms	405mV rms	3	-20 to 60
BS05T1HGNA	5	200mV rms	400mV rms	3	-20 to 60
BS05N1NFAA	5	330mV rms	-	6	-20 to 60
BS05M1KFBB	5	350mV rms	-	10 x 13ch	0 to 50
BS05M1KFCA	5	300mV rms	-	10 x 6ch	0 to 50
BS05M1KGCA	5	150mV rms	-	10 x 6ch	0 to 50
BS05W1KFAA	5	0.3mV p-p	0.8mV p-p	10	-20 to 60
BS05W1KFAB	5	0.3mV p-p	0.8mV p-p	10	-20 to 60

传感器元件

13