





# 冲击传感器



品名	灵敏度型	主轴斜角 (°)	灵敏度*(Typ.) (pC/G)	静电容量 (Typ.) (pF)	谐振频率 (标准值) (kHz)
PKGS-25NB-R	Electric charge sensitivity type	25	0.168	520	44
PKGS-00MF-R	Electric charge sensitivity type	0	0.325	570	27
PKGS-25MF-R	Electric charge sensitivity type	25	0.350	610	27
PKGS-00LD-R	Electric charge sensitivity type	0	0.840	770	20
PKGS-90LD-R	Electric charge sensitivity type	90	0.840	770	20

\*1G=9.80665m/s<sup>2</sup>